

Inductors

Material Data Sheet

Product Class:	ERU13 SMD B82559A****A013
Date	12.02.2018
IMDS ID	
if available	
Version:	05





Version:	05									1	
Product Part (IMDS: semi component)	Material Cla (IMDS: Mate		Material (Classification) VDA 231	Substance			TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)	
Active Part	Ceramic		4B	Manganese Zin	c Ferrite		100	1264549-7	56.6		
	Heavy Metal		1C	Cu		100	7440-50-8	34.6			
	Elastomer		2B	Polyurethane (F	PUR)		100	68400-67-9	1.8		
Encapsulation Duromer			2C	Epoxy resin (EF	P)		100	25068-38-6	1.2		
and Mounting	Organic, solid		5B	Polydimethylsiloxane (MQ)		100	63148-62-9	0.6			
Mounting	Duromer		2C	Polyimide (PI)		100	26298-81-7	0.5			
	Duromer		2C	Acrylic polymer			100	9017-68-9	0.2		
Termination	Heavy Metal		1C	Cu			100	7440-50-8	3.6		
	Heavy Metal		1C	Sn			100	7440-31-5	0.9		
								Sum in total:	100.0		
Size W x L x H [max. in mm] 13.2x11x4.95	nax. in mm] [approx. in g]		Part Numbers			Size W x L x H [max. in mm] 13.2x11x5.95	Wei [approx	c. in g]	Part Numbe		
13.2x11x4.95			82559A0112A013			13.2x11x5.95	2.	6	B82599A0142A	.013	
13.2x11x4.95 2.2 Bi		82559A0222A013			13.2x11x5.95	2.	6	B82559A0242A	.013		
13.2x11x4.95	2.2	В	82559A0302A013			13.2x11x5.95	2.	6	B82559A0392A	.013	
13.9x11x6.5	3.7	В	82559A5232A013								
Not part of a p	roduct class		_				•				
Contact	Dr. Johann Rei	r. Johann Reindl, MAG EPQM				Important remarks:					
Division	TDK Electronic	ctronics AG, Magnetics Business Group (MAG)			1) The d	eclaration limit is 0	1% as define	ed by IEC 62474 (IE	C PAS 61906)	fraces are	
					product parts, substances atc. that are below a percentage of 0.1 % by weight				aight if not		

Contact	Dr. Johann Reindl, MAG EPQM				
Division	TDK Electronics AG, Magnetics Business Group (MAG)				
Address	Rosenheimer Strasse 116b, 81669 Munich				
	Tel: +49 89 54020 3030	mailto:			
		johann.reindl@tdk-electronics.tdk.com			

^{*)} others: .(not declarable or prohibited substances acc. GADSL)

- The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906) Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated
- This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATUENENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

RoHS - Exemptions for the Product Class / Product according to Annex III: (☑ valid □ not valid)

☑ no exemptions;

□ Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;

☐ Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;

☐ Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;

□ Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);

□ Exemption 7 (c)-1: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;

☐ Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;

□ Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;

□ Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

☐ Other Exemption than above

^{**)} typical mass percentage of substance